

XR8001 TEEJET® FLAT SPRAY TIP				
PRESSURE PSI	Dv0.1	Dv0.5	Dv0.9	
10	158	327	523	
20	134	254	428	
30	120	224	386	
40	110	207	363	
50	103	196	348	
60	97	187	338	
70	91	181	332	
80	87	175	329	
90	83	171	324	
100	79	167	318	

XR80015 TEEJET® FLAT SPRAY TIP				
PRESSURE PSI	Dv0.1	Dv0.5	Dv0.9	
10	173	357	546	
20	154	287	467	
30	137	258	427	
40	125	241	400	
50	116	229	381	
60	108	220	365	
70	102	213	353	
80	96	207	342	
90	91	202	334	
100	87	198	326	

XR8002 TEEJET® FLAT SPRAY TIP				
PRESSURE PSI	Dv0.1	Dv0.5	Dv0.9	
10	185	402	588	
20	169	321	503	
30	155	287	459	
40	144	267	430	
50	133	253	409	
60	124	243	393	
70	117	235	379	
80	110	228	368	
90	104	223	358	
100	99	218	350	

XR8003 TEEJET® FLAT SPRAY TIP				
PRESSURE PSI	Dv0.1	Dv0.5	Dv0.9	
10	212	446	614	
20	189	353	536	
30	174	315	495	
40	162	293	468	
50	151	277	448	
60	142	266	432	
70	134	257	419	
80	126	250	409	
90	119	244	399	
100	113	239	391	

XR8004 TEEJET® FLAT SPRAY TIP				
PRESSURE PSI	Dv0.1	Dv0.5	Dv0.9	
10	222	480	683	
20	204	388	601	
30	190	350	553	
40	177	325	519	
50	166	309	492	
60	157	297	471	
70	148	288	452	
80	142	280	436	
90	135	274	422	
100	130	268	410	

XR8005 TEEJET® FLAT SPRAY TIP				
PRESSURE PSI	Dv0.1	Dv0.5	Dv0.9	
10	236	496	745	
20	218	422	664	
30	203	388	614	
40	190	367	576	
50	180	352	545	
60	170	340	519	
70	162	330	495	
80	155	325	474	
90	149	321	455	
100	143	317	437	

XR8006 TEEJET® FLAT SPRAY TIP				
PRESSURE PSI	Dv0.1	Dv0.5	Dv0.9	
10	253	530	795	
20	236	449	738	
30	222	424	694	
40	209	408	656	
50	198	396	622	
60	188	387	592	
70	177	380	563	
80	168	375	537	
90	158	370	512	
100	151	365	488	

XR8008 TEEJET® FLAT SPRAY TIP				
PRESSURE PSI	Dv0.1	Dv0.5	Dv0.9	
10	270	565	862	
20	251	497	806	
30	235	465	761	
40	220	444	721	
50	208	429	684	
60	196	418	649	
70	185	409	617	
80	174	401	587	
90	165	395	559	
100	156	390	532	

NOTE: THE ABOVE DATA APPLIES ONLY TO THE XR TEEJET® EXTENDED RANGE FLAT SPRAY TIPS WITH THE MATERIAL CODES "VS" (STAINLESS STEEL WITH VISIFLO® COLOR-CODING) AND "VP" (POLYMER WITH VISIFLO® COLOR-CODING).

Data is based on spraying water under laboratory conditions using Aerometrics Phase Doppler Particle Analyzer (PDPA).

DESCRIPTION:
XR TEEJET® EXTENDED RANGE
FLAT SPRAY TIP DATA IN
MICRONS VERSUS PRESSURE

CAPACITIES XR8001 THRU XR8008
SPRAYING WATER AT 70° F.



Spraying Systems Co.®

Spray Nozzles and Accessories
P.O. Box 7900 - Wheaton, IL 60189-7900

Rev. No. 1

Ref.

Data Sheet No.

37043-5

SHEET OF