

XR8001 TEEJET® FLAT SPRAY TIP

PRESSURE bar	Dv0.1	Dv0.5	Dv0.9
1	145	283	468
1.5	131	247	419
2	121	227	389
2.5	114	213	370
3	108	203	357
3.5	102	195	347
4	98	189	340
4.5	94	184	335
5	90	179	331
5.5	87	175	329
6	84	172	327

XR80015 TEEJET® FLAT SPRAY TIP

PRESSURE bar	Dv0.1	Dv0.5	Dv0.9
1	164	316	502
1.5	151	281	458
2	139	260	430
2.5	129	246	409
3	122	236	393
3.5	115	228	379
4	110	221	368
4.5	105	216	359
5	100	211	352
5.5	96	207	345
6	93	204	341

XR8002 TEEJET® FLAT SPRAY TIP

PRESSURE bar	Dv0.1	Dv0.5	Dv0.9
1	177	354	541
1.5	166	313	493
2	157	289	462
2.5	148	273	440
3	140	261	422
3.5	133	252	408
4	126	244	396
4.5	120	238	385
5	115	233	376
5.5	110	228	368
6	106	224	361

XR8003 TEEJET® FLAT SPRAY TIP

PRESSURE bar	Dv0.1	Dv0.5	Dv0.9
1	200	391	571
1.5	186	345	527
2	175	318	498
2.5	166	300	477
3	158	287	460
3.5	151	276	447
4	144	268	435
4.5	138	261	425
5	132	255	417
5.5	127	250	409
6	121	246	402

XR8004 TEEJET® FLAT SPRAY TIP

PRESSURE bar	Dv0.1	Dv0.5	Dv0.9
1	214	426	639
1.5	203	379	591
2	192	352	557
2.5	182	333	530
3	174	319	509
3.5	166	308	490
4	159	299	475
4.5	153	292	461
5	147	286	448
5.5	142	280	437
6	138	275	426

XR8005 TEEJET® FLAT SPRAY TIP

PRESSURE bar	Dv0.1	Dv0.5	Dv0.9
1	227	453	702
1.5	215	414	654
2	204	390	618
2.5	195	373	590
3	187	361	565
3.5	179	351	543
4	172	343	524
4.5	166	336	506
5	160	330	490
5.5	155	325	475
6	151	320	460

XR8006 TEEJET® FLAT SPRAY TIP

PRESSURE bar	Dv0.1	Dv0.5	Dv0.9
1	243	471	766
1.5	234	444	729
2	223	426	698
2.5	214	413	670
3	205	404	644
3.5	197	396	620
4	190	389	598
4.5	182	383	576
5	175	378	556
5.5	169	374	537
6	162	370	519

XR8008 TEEJET® FLAT SPRAY TIP

PRESSURE bar	Dv0.1	Dv0.5	Dv0.9
1	261	527	835
1.5	248	490	798
2	236	467	765
2.5	226	451	735
3	216	439	707
3.5	207	428	681
4	198	420	656
4.5	190	413	632
5	182	407	610
5.5	175	401	588
6	167	397	567

NOTE: THE ABOVE DATA APPLIES ONLY TO THE XR TEEJET® EXTENDED RANGE FLAT SPRAY TIPS WITH THE MATERIAL CODES "VS" (STAINLESS STEEL WITH VISIFLO® COLOR-CODING) AND "VP" (POLYMER WITH VISIFLO® COLOR-CODING).

Data is based on spraying water under laboratory conditions using Aerometrics Phase Doppler Particle Analyzer (PDPA).

DESCRIPTION:
XR TEEJET EXTENDED RANGE
FLAT SPRAY TIP DATA IN
MICRONS VERSUS PRESSURE

CAPACITIES XR8001 THRU XR8008
SPRAYING WATER AT 21 DEG. C.



Spraying Systems Co.®

Spray Nozzles and Accessories
P.O. Box 7900 - Wheaton, IL 60189-7900

Rev. No.

Ref.

Data Sheet No.

37043-5M

SHEET OF